



1.25 Gb/s Integrated 850 nm MSM-TIA

Data Sheet - Rev1

FEATURES


- 1.25 Gb/s Differential Output TIA
- 5.0V Operation
- Automatic Gain Control
- 850nm Photodetector with 100 μm²
 Active Area
- Integrated MSM Detector & TIA
- TO46 Lens Package

APPLICATIONS

- Gigabit Ethernet (1.25 Gb/s)
- Fiber Channel (1.0625 Gb/s)

Product Description

The ANADIGICS AMT8100 is a 5V monolithically integrated Metal-Semiconductor-Metal (MSM) photodetector and transimpedance amplifier (TIA) used to convert an 850nm input optical signal into a differential output voltage, and is manufactured in ANADIGICS' 6" GaAs wafer fabrication facility. The integrated MSM and TIA receiver maximizes the receiver performance by minimizing the photodetector input parasitics to the TIA and



internally biasing the photodetector to achieve high sensitivity, bandwidth and overload performance. As an integrated product the reliability is inherently better than a discrete solution, and both the MSM-TIA integrated circuit and TO46 lens packaged receiver pass stringent reliability requirements. These products are readily designed into receivers and transceivers for Gigabit Ethernet and Fibre Channel applications.

Figure 1: AMT8100T46L Equivalent Circuit




Table 1: Absolute Maximum Ratings

V _{DD}	7.0 V
P _{IN}	+ 5 dBm
T _s	Storage Temp 65 °C to 125 °C

Table 2: Electrical Characteristics

PARAMETER	MIN	TYP	MAX	UNIT
Wavelength (λ)	770	850	860	nm
Detector Active Area	-	100 x 100	-	μm²
Small Signal Differential Responsivity (1) (@ 50 MHz)	1000	-	-	VW
Bandwidth (1)	800	-	1500	MHz
Low Frequency Cutoff	-	300	1000	kHz
Output Resistance	25	40	60	Ohm
Optical Overload (2)	0	-	-	dBm
Optical Sensitivity (3)	-20	- 21		dBm
Differential Output Voltage (4), (5)	-	650	-	mV
TRISE & TFALL (20 - 80%) (4), (5)	-	260	-	ps
Duty Cycle Distortion (4), (6)	-	6	10	%
RMS Jitter (4), (6), (7)	-	20	-	ps
Total Jitter (pk-pk) (4), (6), (8)	-	100	-	ps
Supply Current	-	-	50	mA
Operating Voltage Range	4.5	5.0	5.5	V
Operating Ambient Temperature Range	0	-	70	°C


- (1) Measured at –14 dBm optical input power with output connected into R_L = 100 Ω (differential)
- (2) Measured at 10⁻¹² BER with a 2⁷-1 PRBS at 1.25 GB/s
 (3) Measured at 10⁻¹⁰ BER with a 2⁷-1 PRBS at 1.25 Gb/s.
- (4) Input optical power = -3 dBm, R_i = 100 Ω (differential).
- (5) Measured with a 625 MHz, 50% duty cycle square wave.
- (6) Measured with a 1.25 Gb/s, 2⁷-1 PRBS.
- (7) 1_o about the center eye crossing.
- (8) 6_o about the center eye crossing.

Table 3: Package Pin Description

PIN	DESCRIPTION	COMMENT
1	V _{OUT} - TIA Output Voltage (Non-inverted)	Logical '1' with optical input
2	V _{DD} - Positive Supply Voltage	+5 Volts
3	V _{O∪T} - TIA Output Voltage (Inverted)	Logical '0' with optical input
4	Ground	Case is grounded

Figure 2: Eye Diagram with an Optical Input Power Figure 3: Eye Diagram with an Optical Input Power of -17dBm

of -1.0dB







Figure 4: Supply Current vs. Temperature

Figure 5: Bandwidth vs. Temperature







Figure 6: Differential Responsvity vs. Temperature

Figure 7: Sensitivity vs. Temperature






Figure 8: Test Setup for Frequency Response




Figure 9: Test Setup for Sensitivity




Figure 10: Test Setup for Eye Measurements




Figure 11: DUT Test Fixture Schematic





Figure 12: Application Schematic



 $C_{\scriptscriptstyle F}$ is an optional single pole noise filter

$$C_F = \frac{1}{2\pi f c R}$$

 $f_{\scriptscriptstyle c}$ is the desired cutoff frequency

$$R = 50 \Omega$$

 $R_{\scriptscriptstyle O}$ is required with high input resistance limiting amplifiers

$$R_{o}$$
 = 100 Ω

Figure 13: Evaluation Board Schematic




Figure 14: Evaluation Board Layout





Figure 15: T46L Package Outline Diagram



MM CONTROLLING DIMENSIONS

SYMBOL	INCHES		MILLIMETERS		NOTE
-0,	MIN.	MAX.	MIN.	MAX.	
A		0.160		4.00	
øb	0.016	0.020	0.41	0.51	1
øb2	0.012	0.019	0.30	0.48	1
øD	0.212	0.218	5.38	5.54	
ØD1	0.181	0.187	4.60	4.75	
е	0.100 T.P.		2.54	T.P.	2
e 1	0.050 T.P.		1.27 T.P.		2
h	0.014	0.022	0.36	0.56	
1	0.500	0.540	12.70	13.70	1
l 1	_	0.050	-	1.27	1
12	0.250	_	6.35	-	1
G		0.190		4.66	7

NOTES:

- 1. (FOUR LEADS) Øb2 APPLIES BETWEEN l1 AND l2. Øb APPLIES BETWEEN l2 AND 0.5 [12.70mm] FROM SEATING PLANE. DIAMETER IS UNCONTROLLED IN l1 AND BEYOND 0.5 [12.70mm] TO END OF PIN.
- 2. MAXIMUM DIAMETER LEADS AT A GAGING PLANE 0.054
 [1.37mm]+0.001 [0.025mm] -0.000 [0.000mm] BELOW
 SEATING PLANE TO BE WITHIN 0.007 [0.178mm] OF
 THEIR TRUE POSITION RELATIVE TO MAXIMUM—WIDTH TAB
 AND TO THE MAXIMUM 0.212 [5.40mm] DIAMETER
 MEASURED WITH A SUITABLE GAGE. WHEN GAGE IS
 NOT USED, MEASUREMENT WILL BE MADE AT 0.250
 [6.35mm] FROM SEATING PLANE.
- 3. INTERNAL OPTICAL HEIGHT = 0.052±0.003[1.32±0.08] DIE PLACEMENT ACCURACY FOR REF. ONLY.
- 4. BENT LEADS SHOULD NOT EXTEND OUTSIDE DIAMETER (ØD) OF CAP OR TOUCH EACH OTHER.
- 5. ALL DIMENSIONS ARE REFERENCE ONLY-EXCEPT A, D & h.
- 6. DETECTOR DIODE PLACEMENT ACCURACY: $\pm \pm 0.15 \text{MM} [0.006]$ ALL DIRECTIONS
- 7. LENS HEIGHT = 0.65 ± 0.1 [0.026 ± 0.004]

0-022

Ordering Information

Part Number	Package Option	Package Description
AMT8100T46L	TO-46L	Lens Package



ANADIGICS. Inc.

141 Mount Bethel Road Warren, New Jersey 07059, U.S.A

Tel: +1 (908) 668-5000 Fax: +1 (908) 668-5132

http://www.anadigics.com Mktg@anadigics.com

IMPORTANT NOTICE

ANADIGICS, Inc. reserves the right to make changes to its products or discontinue any product at any time without notice. The Advanced Product data sheets and product specifications contained in this data sheet are subject to change prior to a products formal introduction. The information in this data sheet has been carefully checked and is assumed to be reliable. However, ANADIGICS assumes no responsibility for inaccuracies. ANADIGICS strongly urges customers to verify that the information they are using is current before placing orders.

WARNING

ANADIGICS products are not intended for use in life support appliances, devices, or systems. Use of an ANADIGICS product in any such application without written consent is prohibited.