

MS5201-XD (RoHS^{*})

SMD PRESSURE SENSOR



- 1 bar gage pressure range
- Uncompensated
- Piezoresistive silicon micromachined sensor
- Miniature surface mount 7.6 x 7.6 mm
- Low noise, high sensitivity, high linearity
- RoHS-compatible & Pb-free*

DESCRIPTION

The MS5201-XD is a gage type SMD pressure sensor, suitable for applications which require relative (gage) pressure measurements. The device consists of a silicon micromachined pressure sensor die mounted on a 7.6 x 7.6 mm ceramic carrier protected by a plastic cap with a port to connect plastic tube. The MS5201-XD can be delivered in a highly sensitive version giving a maximal output voltage or in a highly linear version giving a linear output voltage directly proportional to the applied pressure.

Full Scale Pressure	High S	Sensitivity Version	High Linearity Version		
	Product Code	Full Scale Span / Linearity	Product Code	Full Scale Span / Linearity	
1 bar	MS5201-AD	240 mV / ±0.2% FS	MS5201-BD	150 mV / ±0.05% FS	

FEATURES

- Low cost SMD ceramic package
- · High reliability, low drift


- -40 °C to +125 °C operation range
- Gel protection


APPLICATION


Medical instrumentation

Pneumatic controls

PIN CONFIGURATION







Top (Pressure to be applied from the top)

^{*} The European RoHS directive 2002/95/EC (Restriction of the use of certain Hazardous Substances in electrical and electronic equipment) bans the use of lead, mercury, cadmium, hexavalent chromium and polybrominated biphenyls (PBB) or polybrominated diphenyl ethers (PBDE).



PIN DESCRIPTION

Pin Name	Pin No.	Function	
OUT-	1	Negative output voltage of Wheatstone bridge	
GND	2	Ground	
VS+	3	Supply voltage of Wheatstone bridge	
OUT+	4	Positive output voltage of Wheatstone bridge	

ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Conditions	Min	Max	Unit
Supply voltage	VS+	Ta = 25°C		20	V
Storage temperature	Ts		-40	+125	°C
Overpressure MS5201-AD MS5201-BD	Р	Ta = 25 °C	-	5 10	bar



ELECTRICAL CHARACTERISTICS

(VS+ = 5 V; Ta = 25 °C)

	Parameter	Min	Тур	Max	Unit	Notes
MS5201-AD	Operating pressure range	0	-	1	bar g	
WOSEOT-AD	Full-scale span (FS)	190	240	290	mV	
High Sensitivity	Sensitivity	190	240	290	mV/bar	
Sensitivity	Linearity	=	240 290 mV			
MS5201-BD	Operating pressure range	0	-	- 1 bar g 240 290 mV 240 290 mV/bar 0.15 ±0.4 % FS - 1 bar g 150 180 mV 150 180 mV/bar 0.05 ±0.2 % FS - 125 °C 0 40 mV 0.05 ±0.15 % FS - 0.3 % FS 0.05 ±0.15 % FS 3.4 3.8 kΩ '900 +3'300 ppm/°C '900 -2'300 ppm/°C		
10100201-00	Full-scale span (FS)	120	150	180	mV	
High	Sensitivity	120	150	180	mV/bar	
Linearity	Operating pressure range 0 - 1 Full-scale span (FS) 190 240 290 Sensitivity 190 240 290 Linearity - ±0.15 ±0.4 Operating pressure range 0 - 1 Full-scale span (FS) 120 150 180 Sensitivity 120 150 180 Linearity - ±0.05 ±0.2 Operating temperature range -40 - 125 Zero pressure offset -40 0 40 Pressure hysteresis - ±0.05 ±0.15 Temperature hysteresis - - 0.3 Repeatability - ±0.05 ±0.15 Bridge resistance 3.0 3.4 3.8 Temperature coefficient of resistance +2'400 2'900 +3'300	% FS	1			
	Operating temperature range	-40	-	125	℃	
All Types	Zero pressure offset	-40	0	40	mV	
	Pressure hysteresis	-	±0.05	±0.15	% FS	2, 6
	Temperature hysteresis	-	-	0.3	% FS	3, 6
	Repeatability	-	±0.05	±0.15	% FS	4, 6
	Bridge resistance	3.0	3.4	3.8	kΩ	
	Temperature coefficient of span	-1'500		-2'300		5, 6 5, 6 5, 6

NOTES

- 1) Deviation at one half full-scale pressure from the least squares best line fit over pressure range.
- 2) Maximum difference of output voltage after 1 pressure cycle at any pressure within the operating pressure range.
- 3) Maximum difference in offset after one thermal cycle from -40 $^{\circ}$ C to +125 $^{\circ}$ C.
- 4) Same as 2) after 10 pressure cycles.
- 5) Slope of the endpoint straight line from 25 °C to 60 °C.
- 6) Not 100% tested.



APPLICATION INFORMATION

GENERAL

The MS5201-XD is a miniaturised gage pressure sensor series which has been designed for surface mounting applications. Its main advantages are the high reliability of the semiconductor sensor and a design which makes it suitable for applications requiring small-scale and cost-efficient solutions.

The sensor element of the MS5201-XD consists of a silicon micromachined membrane with a Pyrex glass and a backside vent hole. Implanted resistors make use of the piezo-resistive effect. The sensor is mounted in a special process allowing best-offset stability making the part suitable for direct PCB assembly.

Typical applications for this miniaturised pressure sensor MS5201-XD are blood pressure monitors or vacuum measurement equipment.

CONNECTION TO PCB

The package outline of the module allows the use of a flexible PCB to connect it. This can be important for certain applications, and will also reduce mechanical stress on the device.

For applications subjected to mechanical shock, it is recommended to enhance the mechanical reliability of the solder junctions by covering the rim or the corners of MS5201-XD ceramic substrate with glue or Globtop-like material.

SOLDERING


Please refer to the application note AN808 for all soldering issues.

CLEANING

The MS5201-XD has been manufactured under cleanroom conditions. Each device has been inspected for the homogeneity and the cleanness of the silicone gel. It is therefore recommended to assemble the sensor under class 10'000 or better conditions. Should this not be possible, it is recommended to protect the sensor opening during assembly from entering particles and dust. To avoid cleaning of the PCB, solder paste of type "no-clean" shall be used. **Cleaning might damage the sensor.**



PACKAGE OUTLINES




Device package outlines of MS5201-XD (plastic cap, gel protection of bonding wires)



RECOMMENDED PAD LAYOUT

Recommended pad layout for soldering of the MS5201-XD on a printed circuit board



*Recommended vent hole diameter

ORDERING INFORMATION

Product Code	Product	ArtNr.	Package	Comment
MS5201-AD	Pressure sensor 1 bar High sensitivity	325201001	SMD hybrid with solder bumps, plastic cap, drop of gel on	
MS5201-BD	Pressure sensor 1 bar High linearity	325201003	sensor, no gel protection of the bonding wires	

FACTORY CONTACTS

Intersema Sensoric SA Tel. 032 847 9550
Ch. Chapons-des-Prés 11 Tel. Int. +41 32 847 9550
CH-2022 BEVAIX Telefax +41 32 847 9569

e-mail: <u>sales@intersema.ch</u>
SWITZERLAND <u>http://www.intersema.ch</u>

NOTICE

Intersema reserves the right to make changes to the products contained in this data sheet in order to improve the design or performance and to supply the best possible products. Intersema assumes no responsibility for the use of any circuits shown in this data sheet, conveys no license under any patent or other rights unless otherwise specified in this data sheet, and makes no claim that the circuits are free from patent infringement. Applications for any devices shown in this data sheet are for illustration only and Intersema makes no claim or warranty that such applications will be suitable for the use specified without further testing or modification.